


10x18 AWG ITC PLTC AWM 2586 105C 600V

SPECIFICATIONS

- A 18 AWG 19x.0092" UNILAY TINNED COPPER
- B PVC INSULATION
- C FILLER
- D 20 AWG TINNED COPPER DRAIN WIRE
- E ALUMINUM/POLYESTER FOIL SHIELD (FOIL IN)
- F PRESSURED PVC JACKET
JACKET COLOR: BLACK
CABLE IS RoHS COMPLIANT, CE

CONDUCTOR COLORS

- 1 = BLACK
- 2 = WHITE
- 3 = YELLOW
- 4 = VIOLET
- 5 = GRAY
- 6 = GREEN/YELLOW
- 7 = RED
- 8 = ORANGE
- 9 = BLUE
- 10 = BROWN



MECHANICAL REQUIREMENTS
 STATIC: 5x CABLE O.D.
 FLEX SHIELDED: 15x CABLE O.D.

NOTES:

1. WHITE INK
 101550553 18 AWG/10 (UL) ITC 105C UL# SUNLIGHT RESISTANT OR PLTC 105C -40C OIL RES I & II OR AWM 105C 600V OR CSA CMX OUTDOOR-CMG CSA# 105C OR CSA AWM I/II A/B 105C 600V FT4 MSHA# CE SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))
2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS

NOTE: CONDUCTOR ROTATION MAY BE INVERTED FROM VIEW SHOWN **SOURCE DRAWING - FOR REFERENCE ONLY**

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
	MATERIAL SEE SPECIFICATIONS	DRFT RDS APVD S.F.	DATE 12/14/11 SCALE NONE	DESCRIPTION CAB,10,8,BLK,PVC,10X18,S-,ITC	
FINISH SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT INCH [MILLIMETER]		IDENTIFICATION NO. 101550553 (SOURCE)	REV D
D UPDATE TO "GREEN/YELLOW", ADD "CE"	RDS 05/30/17	60381		FILE: 101550553	
REV DESCRIPTION	BY DATE	ECO NO.		SHEET 1 OF 1	