

FEMALE END VIEW


1 = BROWN  
2 = WHITE  
3 = BLUE  
4 = BLACK  
5 = DRAIN

MALE END VIEW

1 = BROWN  
2 = WHITE  
3 = BLUE  
4 = BLACK  
5 = DRAIN

SPECIFICATIONS

CONTACT CARRIER MATERIAL	NYLON OR TPU
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
OUTER CABLE JACKET MATERIAL/COLOR	PVC/GRAY
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	4x22 AWG
DRAIN/SHIELD	24 AWG/ALUMI.-POLYESTER FOIL
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

2. "/S653" DESIGNATES CABLE WITH FOIL SHIELD AND DRAIN. DRAIN IS CONNECTED TO A PIN AT THE CONNECTOR.

RELATED DOCUMENTS

1.

2.

3.

4.

3RD ANGLE PROJECTION

THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.

3000 CAMPUS DRIVE  
MINNEAPOLIS, MN 55441  
1-800-544-7769  
(763) 553-7300  
(763) 553-0708 fax  
www.turck.us

MATERIAL

FINISH

DRFT MJM

APVD

DATE 06/07/06

SCALE 1=1.0

DESCRIPTION WK 4.5T-\*--WS 4.5T/S653

UNIT OF MEASUREMENT MILLIMETER [ INCH ]

IDENTIFICATION NO.

REV F

CONTACT TURCK FOR MORE INFORMATION

DO NOT SCALE THIS DRAWING

FILE: 777000422

SHEET 1 OF 1

F	UPDATE MALE COUPLING NUT	RDS	04/24/18	56902
REV	DESCRIPTION	BY	DATE	ECO NO.