


SPECIFICATIONS					
CONTACT CARRIER MATERIAL/COLOR	TPU/YELLOW				
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW				
CONTACT MATERIAL/PLATING	BRASS/GOLD				
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL				
RATED CURRENT [A]	10.0 A				
RATED VOLTAGE [V]	600 V				
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW				
NUMBER OF CONDUCTORS [AWG]	3x16 AWG				
CONDUCTOR INSULATION MATERIAL	PVC				
TEMPERATURE RATING	-40° C to $+105^{\circ}$ C (-40° F to $+221^{\circ}$ F)				
PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K				



CABLE LENGTH	TOLERANCE *			
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER			
STRIP LENGTH TOLERANCE *				
0-7mm	±0.5mm			
8-29mm	±1.0mm			
30-49mm	±2.0mm			
50-69mm	±3.0mm			
70-100mm	±4.0mm			
OVER 100mm	±5.0mm			
* UNLESS OTHERWISE SPECIFIED				

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

F	UPDATE PROTECTION CLASS	СВМ	04/13/21	76628
REV	DESCRIPTION	BY	DATE	ECO NO.

SOURCE DRAWING - FOR REFERENCE ONLY

	RELATED DOCUMENTS 1. RJP 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		IRC		(763) (763)	LIS, MN -544-7 553-7	55441 7769 300 708 fax
	MATERIAL		DRFT RJP	DATE 10/05/93	DESCRIPTION	DIZM 70	***		
	SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.0		RKM 36	>* VI		
		DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT		105175017011111				55.
f	FINISH	THE ENERGE ONE			IDENTIFICATION NO.				REV
		CONTACT TURCK FOR MORE	MILLIMETE	ER [INCH]					F
	SEE SPECIFICATIONS	INFORMATION							
			DO NOT SCALE	THIS DRAWING FILE: 777000779				SHEET	1 OF
					•			•	