


SPECIFICATIONS					
CONTACT CARRIER MATERIAL/COLOR	TPU/YELLOW				
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW				
CONTACT MATERIAL/PLATING	BRASS/GOLD				
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL				
RATED CURRENT [A]	10.0 A				
RATED VOLTAGE [V]	600 V				
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW				
CONDUCTORS	4x16 AWG				
CONDUCTOR INSULATION MATERIAL	PVC				
TEMPERATURE RATING	-40°C to +105°C (-40°F to +221°F)				
PROTECTION CLASS NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K					



CABLE LENGTH	TOLERANCE *		
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER		
STRIP LENGTH	TOLERANCE *		
0-7mm	±0.5mm		
8-29mm	±1.0mm		
30-49mm	±2.0mm		
50-69mm	±3.0mm		
70-100mm	±4.0mm		
OVER 100mm	±5.0mm		
* UNLESS OTHERWISE SPECIFIED			

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		rck	(763) (763)	LIS, MN -544-7 553-7	55441 7769 300 708 fax
MATERIAL		DRFT JBJ	DATE 05/05/99	DESCRIPTION RSM RKM	16 *M	1	
SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.3	NOW KNIN	40- IVI		
522	DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT		IDENTIFICATION NO.		-	REV
FINISH	CONTACT TURCK	MILLIMETE	R [INCH]	IDENTIFICATION NO.			1
SEE SPECIFICATIONS	FOR MORE INFORMATION						J
SEE SI EON IO/MIONS	nu enim	DO NOT SCALE	THIS DRAWING	FILE: 777001023		SHEET	1 OF 1

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

L					
	ے	UPDATE PROTECTION CLASS	СВМ	04/13/21	76628
I	REV	DESCRIPTION	BY	DATE	ECO NO.