


SPECIFICATIONS						
CONTACT CARRIER MATERIAL	TPU/BLUE-GRAY					
MOLDED HEAD MATERIAL/COLOR	TPU/BLUE-GRAY					
CONTACT MATERIAL/PLATING	BRASS/GOLD					
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL					
RATED CURRENT [A]	4.0 A					
RATED VOLTAGE [V]	250 V					
OUTER JACKET MATERIAL/COLOR	PVC/GREY					
CONDUCTOR INSULATION MATERIAL	HDPE (DATA), SRPVC (POWER)					
NUMBER OF CONDUCTORS [AWG]	4x22 AWG, 22 AWG DRAIN					
SHIELDING	FOIL (PAIRS), FOIL (OVERALL)					
TEMPERATURE RATING	-40°C to +80°C (-40°F to +176°F)					
PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP68, IP69K					



CABLE LENGTH	TOLERANCE *				
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER				
STRIP LENGTH	TOLERANCE *				
0-7mm	±0.5mm				
8-29mm	±1.0mm				
30-49mm	±2.0mm				
50-69mm	±3.0mm				
70-100mm	±4.0mm				
OVER 100mm	±5.0mm				
* UNLESS OTHERWISE SPECIFIED					

## NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

E	UPDATE RATED VOLTAGE	RDS	08/06/19	75160
REV	DESCRIPTION	BY	DATE	ECO NO.

## SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS  1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		rck	3000 CAMPUS MINNEAPOLIS, MN 1-800-544-7 (763) 553-7 (763) 553-0 www.turck.u	1 55441 7769 300 708 fax
MATERIAL	ALL DIMENSIONS DISPLAYED ON THIS	DRFT CBM APVD	DATE 12/17/01 SCALE 1=1.0	DESCRIPTION RKC RKC	572-*M	
FINISH	DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION	CK MILLIMET	ASUREMENT	IDENTIFICATION NO.		rev E
	INFORMATION	DO NOT SCALE THIS DRAWING		FILE: 777005250	SHEET	1 OF 1