


SPECIFICATIONS					
TPU OR NYLON					
TPU/YELLOW					
BRASS/GOLD					
BRASS/NICKEL					
4.0 A					
250 V					
TPE/YELLOW					
PVC					
4x22 AWG					
-40°C to +105°C (-40°F to +221°F)					
MEETS NEMA 1,3,4,6P AND IEC IP69K					



CABLE LENGTH	TOLERANCE *			
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER			
STRIP LENGTH	TOLERANCE *			
0-7mm	±0.5mm			
8-29mm	±1.0mm			
30-49mm ±2.0mm				
50-69mm	±3.0mm			
70-100mm ±4.0mm				
OVER 100mm	OVER 100mm ±5.0mm			
*UNLESS OTHERWISE SPECIFIED				

NOTES:

- 1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- 2. "/S1587" DESIGNATES WELDLIFE JACKETED CABLE.

F UPDATE TEMPERATURE RANGE NF 08/07/17 61664 SEE SPECIFICATIONS INFORMATION						THISH	CONTACT TURCK	MILL
REV DESCRIPTION BY DATE ECO NO. DO 1	Ŧ	UPDATE TEMPERATURE RANGE	NF	08/07/17	61664	SEE SPECIFICATIONS	FOR MORE INFORMATION	
	REV	DESCRIPTION	BY	DATE	ECO NO.			DO NO

SOURCE DRAWING - FOR REFERENCE ONLY

	RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		RCK	3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us
I	MATERIAL		DRFT RDS	DATE 10/31/05	DESCRIPTION RK 4.4T-*-RS	1 1T/C1E07
ı	SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.0	KK 4.41-*-KS	4.41/3130/
ı		DRAWING ARE FOR REFERENCE ONLY	UNIT OF ME	ASUREMENT	URENTIERO TION NO	I DD/
ı	FINISH	THE ENERGE SITE			IDENTIFICATION NO.	REV
$\frac{1}{1}$	SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION		ER [INCH]		F
	SEE SPECIFICATIONS	INFORMATION	DO NOT SCALE	THIS DRAWING	FILE: 777008487	SHEET 1 OF 1