
FEMALE END VIEW	SPECIF	SPECIFICATIONS		
	CONTACT CARRIER MATERIAL	NYLON OR TPU		
	MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW		
	CONTACT MATERIAL/PLATING	BRASS/GOLD		
	COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL		
	RATED CURRENT [A]	4.0 A		
$\mathbf{\Psi}$	RATED VOLTAGE [V]	250 V		
1 $1 = GREEN/YELLOW$ $2 = RED/BLACK$ $3 = RED/WHITE$	OUTER CABLE JACKET MATERIAL/COLOR	PVC/YELLOW		
	CONDUCTOR INSULATION MATERIAL	PVC		
	NUMER OF CONDUCTORS [AWG]	3x18 AWG		
	TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)		
milero Vast.	PROTECTION CLASS	NEMA 1,3,4,6 AND IEC IP67, IP68, IP69K		



CABLE LENGTH	TOLERANCE *			
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER			
STRIP LENGTH	TOLERANCE *			
0-7mm	±0.5mm			
8–29mm	±1.0mm			
30-49mm	±2.0mm			
50-69mm	±3.0mm			
70–100mm	±4.0mm			
OVER 100mm	±5.0mm			
* UNLESS OTHERWISE SPECIFIED				

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND PROPERTY OF TUR INC. USE OF THIS DOCUMENT WITHON WRITTEN PERMISSION PROHIBITED.		RC	MINNEAP(1-800 (763) (763))-544-1 553-7	l 55441 7769 300 708 fax
MATERIAL		^{DRFT} RDS	DATE 10/19/06	DESCRIPTION	KBF 3T-*		
SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.0]	KDE JI-		
	DRAWING ARE FOR REFERENCE ONLY	UNIT OF	MEASUREMENT				
FINISH				IDENTIFICATION NO.			REV
	CONTACT TURCK	MILLIME	TER [INCH]				F
SEE SPECIFICATIONS	INFORMATION						L
		DO NOT SC	ALE THIS DRAWING	FILE: 777010026		SHEET	1 OF 1

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

Е	UPDATE CONDUCTOR COLOR	NF	01/30/18	61368	SEE SPECIFICATIONS
REV	DESCRIPTION	BY	DATE	ECO NO.	