


FEMALE END VIEW	MALE END VIEW	SPECIFICATIONS	
 <p>1 = BROWN 3 = BLUE 4 = BLACK</p>	 <p>1 = BROWN 2 = N/C 3 = BLUE 4 = BLACK</p>	CONTACT CARRIER MATERIAL/COLOR	NYLON or TPU/BLACK (J1), YELLOW (P1)
		MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
		CONTACT MATERIAL/PLATING	BRASS/GOLD
		LOCKING SLEEVE (J1)	POM, SNAP LOCK
		COUPLING NUT MATERIAL/PLATING (P1)	BRASS/NICKEL
		RATED CURRENT [A]	4.0 A
		RATED VOLTAGE [V]	125 VAC/VDC
		OUTER JACKET MATERIAL/COLOR	TPU/BLACK
		CONDUCTOR INSULATION MATERIAL	PVC
		NUMBER OF CONDUCTORS [AWG]	3x24 AWG
		TEMPERATURE RANGE	-40°C to +90°C (-40°F to +194°F)
		PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67





CABLE LENGTH	TOLERANCE*
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE*
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
* UNLESS OTHERWISE SPECIFIED	

NOTES:

- "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- "/S90" INDICATES THERMOPLASTIC POLYURETHANE (TPU) CABLE.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us
		DRFT CK APVD	DATE 04/12/11 SCALE 1=1.0
MATERIAL SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT MILLIMETER [INCH]	DESCRIPTION PKG 3Z-*--WS 4T/S90
FINISH SEE SPECIFICATIONS		DO NOT SCALE THIS DRAWING	IDENTIFICATION NO. 777015619
REV	DESCRIPTION	BY	DATE
C	UPDATE M12 COUPLING NUT	RDS	04/23/18 56903
ECO NO.	BY	DATE	ECO NO.
FILE: 777015619		SHEET 1 OF 1	