


SPECIFICATIONS				
CONTACT CARRIER MATERIAL	NYLON OR TPU			
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW			
CONTACT MATERIAL/PLATING	BRASS/GOLD			
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL			
RATED CURRENT [A]	4.0 A			
RATED VOLTAGE [V]	125 VAC/VDC			
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW			
CONDUCTOR INSULATION MATERIAL	PVC			
NUMBER OF CONDUCTORS [AWG]	3x24 AWG			
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)			
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68			



CABLE LENGTH	TOLERANCE *			
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER			
STRIP LENGTH	TOLERANCE *			
0-7mm	±0.5mm			
8-29mm	±1.0mm			
30-49mm	±2.0mm			
50-69mm	±3.0mm			
70-100mm	±4.0mm			
OVER 100mm	±5.0mm			
* UNLESS OTHERWISE SPECIFIED				

## NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

					SEE	SPECIFICATIONS	DISPLAYED DRAWING REFEREN
l					FINISH		1
							CONTACT
D	UPDATE COUPLING NUT PER ECO	KMY	05/09/13	40191	SEE	SPECIFICATIONS	FOR INFORM
REV	DESCRIPTION	BY	DATE	ECO NO.			
							-

## SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS  1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		RCI	MINNEAPO 1-800- (763) (763)	AMPUS DR LIS, MN 5 -544-776 553-730 553-070 1.turck.us	5441 59 0
SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR		DATE 03/01/01  SCALE 1=1.0  ASUREMENT	description F	°SG 3M-*		
FINISH SEE SPECIFICATIONS	REFERENCE ONLY  CONTACT TURCK FOR MORE INFORMATION	MILLIMETE		IDENTIFICATION NO.			REV D
		DO NOT SCALE THIS DRAWING		FILE: 777000852	·	SHEET 1	OF 1