









MALE END VIEW		FEMALE END VIEW	SPECIFICATIONS	
			CONTACT CARRIER MATERIAL	TPU
 M16 connector		 M16 connector	MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
			CONTACT MATERIAL/PLATING	BRASS/GOLD
			COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
			RATED CURRENT [A]	3.0 A
			RATED VOLTAGE [V]	30 VAC/VDC
			OUTER JACKET MATERIAL/COLOR	PVC/BLACK
			CONDUCTOR INSULATION MATERIAL	PVC
			NUMBER OF CONDUCTORS [AWG]	12x24 AWG
			DRAIN/SHIELD	26 AWG DRAIN/ALUMINUM FOIL SHIELD
			TEMPERATURE RANGE	-40°C TO +105°C (-40°F TO +221°F)
			PROTECTION CLASS	MEETS IEC IP67

																																																			
<table><tr><th>CABLE LENGTH</th><th>TOLERANCE*</th></tr><tr><td>ALL LENGTHS</td><td>+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER</td></tr><tr><th>STRIP LENGTH</th><th>TOLERANCE*</th></tr><tr><td>0-7mm</td><td>±0.5mm</td></tr><tr><td>8-29mm</td><td>±1.0mm</td></tr><tr><td>30-49mm</td><td>±2.0mm</td></tr><tr><td>50-69mm</td><td>±3.0mm</td></tr><tr><td>70-100mm</td><td>±4.0mm</td></tr><tr><td>OVER 100mm</td><td>±5.0mm</td></tr></table> <p>* UNLESS OTHERWISE SPECIFIED</p>		CABLE LENGTH	TOLERANCE*	ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER	STRIP LENGTH	TOLERANCE*	0-7mm	±0.5mm	8-29mm	±1.0mm	30-49mm	±2.0mm	50-69mm	±3.0mm	70-100mm	±4.0mm	OVER 100mm	±5.0mm	SOURCE DRAWING - FOR REFERENCE ONLY																															
CABLE LENGTH	TOLERANCE*																																																		
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER																																																		
STRIP LENGTH	TOLERANCE*																																																		
0-7mm	±0.5mm																																																		
8-29mm	±1.0mm																																																		
30-49mm	±2.0mm																																																		
50-69mm	±3.0mm																																																		
70-100mm	±4.0mm																																																		
OVER 100mm	±5.0mm																																																		
NOTES: 1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.		<table><tr><td rowspan="2">RELATED DOCUMENTS 1. 2. 3. 4.</td><td rowspan="2">3RD ANGLE PROJECTION </td><td rowspan="2">THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</td><td colspan="2"><div>TURCK INC</div><div>High Technology Sensors and Automation Controls</div><div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div></td></tr><tr><td colspan="2">DESCRIPTION BSM BKM 14-755-*</td></tr><tr><td>MATERIAL SEE SPECIFICATIONS</td><td rowspan="8">ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</td><td>DRFT</td><td>JBJ</td><td>DATE</td><td>06/09/03</td></tr><tr><td>FINISH SEE SPECIFICATIONS</td><td>APVD</td><td></td><td>SCALE</td><td>1=1.0</td></tr><tr><td colspan="2"></td><td colspan="2">UNIT OF MEASUREMENT MILLIMETER [INCH]</td></tr><tr><td colspan="2"></td><td colspan="2">IDENTIFICATION NO.</td><td>REV</td></tr><tr><td colspan="2"></td><td colspan="2">DO NOT SCALE THIS DRAWING</td><td></td></tr><tr><td colspan="2"></td><td colspan="2">FILE: 777002083</td><td>SHEET 1 OF 1</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td></td></tr><tr><td colspan="2"></td><td colspan="2"></td><td></td></tr></table>			RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<div>TURCK INC</div> <div>High Technology Sensors and Automation Controls</div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div>		DESCRIPTION BSM BKM 14-755-*		MATERIAL SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	JBJ	DATE	06/09/03	FINISH SEE SPECIFICATIONS	APVD		SCALE	1=1.0			UNIT OF MEASUREMENT MILLIMETER [INCH]				IDENTIFICATION NO.		REV			DO NOT SCALE THIS DRAWING					FILE: 777002083		SHEET 1 OF 1										
RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<div>TURCK INC</div> <div>High Technology Sensors and Automation Controls</div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div>																																																
			DESCRIPTION BSM BKM 14-755-*																																																
MATERIAL SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	JBJ	DATE	06/09/03																																														
FINISH SEE SPECIFICATIONS		APVD		SCALE	1=1.0																																														
		UNIT OF MEASUREMENT MILLIMETER [INCH]																																																	
		IDENTIFICATION NO.		REV																																															
		DO NOT SCALE THIS DRAWING																																																	
		FILE: 777002083		SHEET 1 OF 1																																															
I	UPDATE CABLE DIAMETER	KMY	01/27/12	37169																																															
REV	DESCRIPTION	BY	DATE	ECO NO.																																															