





### FIGURE 10 FEMALE END VIEW



1 = BROWN  
2 = WHITE  
3 = BLUE  
4 = BLACK  
5 = GREY  
6 = PINK





SPECIFICATIONS	
CONTACT CARRIER MATERIAL	NYLON OR TPU
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/FINISH	STAINLESS STEEL/PASSIVATED
RATED CURRENT [A]	1.5 A
RATED VOLTAGE [V]	30 VAC/36 VDC
OUTER CABLE JACKET MATERIAL/COLOR	PVC/GREY
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	6x24 AWG, 26 AWG DRAIN
SHIELDING	ALUMINUM/POLYESTER FOIL
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP68, IP69K



CABLE LENGTH	TOLERANCE *
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE *
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
<b>* UNLESS OTHERWISE SPECIFIED</b>	

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

E	UPDATE CABLE	CK	07/07/11	34922
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<div style="text-align: center;">  <p><b>TURCK INC</b></p> <p><i>High Technology Sensors and Automation Controls</i></p> </div> <div style="text-align: right;">             3000 CAMPUS DRIVE              MINNEAPOLIS, MN 55441              1-800-544-7769              (763) 553-7300              (763) 553-0708 fax              turck.com           </div>		
						
	MATERIAL	DRFT	RDS	DATE	01/14/05	DESCRIPTION
	SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DSGN	SCALE	1=1.0	
FINISH		UNIT OF MEASUREMENT			IDENTIFICATION NO.	
SEE SEPCIFICATIONS	CONTACT TURCK FOR MORE INFORMATION	MILLIMETER [ INCH ]				E
		DO NOT SCALE THIS DRAWING			FILE: 777003760	