



SPECI	FICATIONS
SPECIFICATIONS	
CONTACT CARRIER MATERIAL	NYLON OR TPU
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/COLOR	BLACK/NYLON
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
OUTER CABLE JACKET MATERIAL/COLOR	PVC/GRAY
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	3x22 AWG
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68





CABLE LENGIN	IOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE *
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
* UNLESS OT	HERWISE SPECIFIED

2.

3.

44672

ECO NO.

KMY 05/22/14

DATE

## SOURCE DRAWING - FOR REFERENCE ONLY

FILE: 777000735

1-800-544-7769

(763) 553-7300

(763) 553-0708 fax turck.com

REV

SHEET 1 OF 1

## NOTES:

REV DESCRIPTION

UPDATE CABLE SPECIFICATIONS

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

RELATED DOCUMENTS 3RD ANGLE PROJECTION THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 turck iac DOCUMENT WITHOUT
WRITTEN PERMISSION IS
PROHIBITED. High Technology Sensors and Automation Controls MATERIAL DATE 11/08/07 DESCRIPTION RWC WKK 4T-\* ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR SCALE 1=1.0 APVD SEE SPECIFICATIONS UNIT OF MEASUREMENT REFERENCE ONLY IDENTIFICATION NO. FINISH CONTACT TURCK FOR MORE INFORMATION MILLIMETER [ INCH ] SEE SPECIFICATIONS

DO NOT SCALE THIS DRAWING