



CABLE LENGTH	1 TOLERANCE				
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER				
STRIP LENGTH	TOLERANCE				
0-7mm	±0.5mm				
8–29mm	±1.0mm				
30-49mm	±2.0mm				
50-69mm	±3.0mm				
70-100mm	±4.0mm				
OVER 100mm	±5.0mm				

SOURCE DRAWING - FOR REFERENCE ONLY

	RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.			000 CAMPUS INEAPOLIS, MN 1-800-544- (763) 553-7 (763) 553-0 turck.com	V 55441 7769 300 708 fax
	MATERIAL		DRFT RDS	DATE 08/06/02	DESCRIPTION E-RKS 8T-9	z∩ *	
	SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	DSGN	SCALE 1=1.0	E = RKS SI = 9	50-1	
		DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT				55/
	FINISH	KEI EKENGE ONEI			IDENTIFICATION NO.		REV
26	SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION		Er [INCH]			В
NO.			DO NOT SCALE	THIS DRAWING	FILE: 777001265	SHEET	1 OF 1

NOTES:

1."*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

2. COUPLING NUT IS CONNECTED TO SHIELD.

В	UPDATE PROTECTION CLASS	RDS	02/10/11	34226	SEE SPECIFICATIONS
REV	DESCRIPTION	BY	DATE	ECO NO.	