







MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS	
 <div>1 = WHITE 2 = GREEN 3 = YELLOW 4 = GRAY 5 = PINK 6 = RED 7 = BLACK 8 = VIOLET 9 = N/C 10 = BLUE 11 = BROWN 12 = GRN/YEL</div>		 <div>1 = WHITE 2 = GREEN 3 = YELLOW 4 = GRAY 5 = PINK 6 = RED 7 = BLACK 8 = VIOLET 9 = N/C 10 = BLUE 11 = BROWN 12 = GRN/YEL</div>		CONTACT CARRIER MATERIAL/COLOR	NYLON or PBT/GRAY
 M23 connector		 M23 connector		MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
				CONTACT MATERIAL/PLATING	BRASS/GOLD
				COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
				RATED CURRENT [A]	6.0 A
				RATED VOLTAGE [V]	300 V
				OUTER JACKET MATERIAL/COLOR	TPU/YELLOW
				CONDUCTOR INSULATION MATERIAL	PVC
				NUMBER OF CONDUCTORS	11x18 AWG
				DRAIN/SHIELD	20 AWG/ALUM.-POLYESTER FOIL
				TEMPERATURE RATING	-40°C to +105°C (-40°F to +221°F)
				PROTECTION CLASS	IEC IP67



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS				3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1. 2. 3. 4.						DRFT RWC		DATE 04/20/06	
MATERIAL				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DSGN		SCALE 1=1.5	
SEE SPECIFICATIONS				CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT		DESCRIPTION	
FINISH						MILLIMETER [INCH]		CSCM CKCM 12-11-*/S90	
SEE SPECIFICATIONS						DO NOT SCALE THIS DRAWING		IDENTIFICATION NO.	
D DRAWING PROCESSED AS PART OF ECO 33971				BY		DATE		REV	
ECO NO.								D	
DESCRIPTION						FILE: 777008906		SHEET 1 OF 1	