






RJ45S END VIEW	PANEL CUTOUT	LOCKNUT	SPECIFICATIONS	
<div></div> <div>12345678</div> <div><div>1 = WHITE/ORANGE (+TX)</div><div>2 = ORANGE (-TX)</div><div>3 = WHITE/GREEN (+RX)</div><div>4 = BLUE</div><div>5 = WHITE/BLUE</div><div>6 = GREEN (-RX)</div><div>7 = WHITE/BROWN</div><div>8 = BROWN</div></div> <div><div>Ethernet</div></div>	<div></div> <div>ø20.42 [ø0.804]</div>	<div></div> <div>(2x) 10161546 LOCKNUT PLACED IN BAG</div>	<div><div>CONTACT CARRIER MATERIAL (RJ45S)</div><div>MOLDED MATERIAL/COLOR (RJ45S)</div><div>CONTACT MATERIAL/PLATING (RJ45S)</div><div>RATED CURRENT [A]</div><div>RATED VOLTAGE [V]</div><div>OUTER CABLE JACKET MATERIAL/COLOR</div><div>INNER CABLE JACKET MATERIAL/COLOR</div><div>CONDUCTOR INSULATION MATERIAL</div><div>NUMBER OF CONDUCTORS [AWG]</div><div>SHIELDING</div><div>TEMPERATURE RANGE</div></div> <div><div>POLYCARBONATE</div><div>TPU/BLACK</div><div>BRONZE/GOLD</div><div>1.5 A</div><div>42 V</div><div>TPU/BLACK</div><div>TPE/NATURAL</div><div>FOAMED HDPE</div><div>4UTPX26AWG, STRANDED</div><div>TINNED-COPPER BRAIDED</div><div>-30°C to +80°C (-22°F to +176°F)</div></div>	



NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
2. "/C1186" INDICATES:
- ADDITION OF CABLE GLAND (10130074) TO BOTH ENDS OF THE CABLE AT 0.5M UP FROM END OF EACH CONNECTOR.
 - ADDITION OF LOCK NUT (10161546) TO EACH CABLE GLAND.
 - CUSTOM OVERALL LENGTH TOLERANCE.
 - PROTECTIVE RJ45 CAPS ATTACHED TO ASSEMBLY BEFORE SHIPPING.

SOURCE DRAWING - FOR REFERENCE ONLY

<div>1. "★" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.</div> <div>2. "/C1186" INDICATES:<ul style="list-style-type: none">ADDITION OF CABLE GLAND (10130074) TO BOTH ENDS OF THE CABLE AT 0.5M UP FROM END OF EACH CONNECTOR.ADDITION OF LOCK NUT (10161546) TO EACH CABLE GLAND.CUSTOM OVERALL LENGTH TOLERANCE.PROTECTIVE RJ45 CAPS ATTACHED TO ASSEMBLY BEFORE SHIPPING.</div> <table><tr><td>K</td><td>UPDATE CONDUCTOR CALLOUT</td><td>RDS</td><td>04/10/17</td><td>59429</td></tr><tr><td>REV</td><td>DESCRIPTION</td><td>BY</td><td>DATE</td><td>ECO NO.</td></tr></table>					K	UPDATE CONDUCTOR CALLOUT	RDS	04/10/17	59429	REV	DESCRIPTION	BY	DATE	ECO NO.	RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
					K	UPDATE CONDUCTOR CALLOUT	RDS	04/10/17	59429													
					REV	DESCRIPTION	BY	DATE	ECO NO.													
					1. 2. 3. 4.				TURCK													
					MATERIAL		<div>ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</div> <div>CONTACT TURCK FOR MORE INFORMATION</div>		DRFT RDS		DATE 08/07/07		DESCRIPTION RJ45S RJ45S 8413-★M/C1186									
		APVD		SCALE 1 = 1.3																		
FINISH				UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO.				REV K												
				DO NOT SCALE THIS DRAWING		FILE: 777018831				SHEET 1 OF 1												