






MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS	
 <div>1 = ORANGE 2 = BLUE 3 = WHITE/BLACK 4 = RED/BLACK 5 = GREEN/BLACK 6 = ORANGE/BLACK 7 = BLUE/BLACK 8 = BLACK/WHITE 9 = GREEN/YELLOW 10 = RED 11 = WHITE 12 = BLACK</div> 		 <div>1 = ORANGE 2 = BLUE 3 = WHITE/BLACK 4 = RED/BLACK 5 = GREEN/BLACK 6 = ORANGE/BLACK 7 = BLUE/BLACK 8 = BLACK/WHITE 9 = GREEN/YELLOW 10 = RED 11 = WHITE 12 = BLACK</div> 		CONTACT CARRIER MATERIAL/COLOR	TPU/YELLOW
				MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
				CONTACT MATERIAL/PLATING	BRASS/GOLD
				COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
				RATED CURRENT [A]	7.0 A
				RATED VOLTAGE [V]	600 V
				OUTER JACKET MATERIAL/COLOR	TPE/YELLOW
				CONDUCTOR INSULATION MATERIAL	POLYESTER ELASTOMER
				NUMBER OF CONDUCTORS	12x16 AWG
				TEMPERATURE RATING	-40°C to +105°C (-40°F to +221°F)
				PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K






CABLE LENGTH	TOLERANCE *
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE *
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
* UNLESS OTHERWISE SPECIFIED	

NOTES:

- "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- "/S101" DESIGNATES FLEXLIFE-20 AND C-TRACK CABLE.

SOURCE DRAWING - FOR REFERENCE ONLY

<div>NOTES:</div> <div>1. "＊" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.</div> <div>2. "/S101" DESIGNATES FLEXLIFE-20 AND C-TRACK CABLE.</div>					<table><tr><td colspan="2">RELATED DOCUMENTS</td><td colspan="2">3RD ANGLE PROJECTION</td><td colspan="2" rowspan="2"><div>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div><div>TURCK</div><div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</div></td></tr><tr><td colspan="2">1. 2. 3. 4.</td><td colspan="2"></td></tr></table>		RELATED DOCUMENTS		3RD ANGLE PROJECTION		<div>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div> <div>TURCK</div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</div>		1. 2. 3. 4.																																	
					RELATED DOCUMENTS		3RD ANGLE PROJECTION		<div>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div> <div>TURCK</div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</div>																																					
1. 2. 3. 4.																																														
<table><tr><td colspan="2">MATERIAL</td><td colspan="2" rowspan="2">ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</td><td colspan="2">DRFT</td><td colspan="2">RDS</td><td colspan="2">DATE 06/08/09</td><td colspan="2" rowspan="2">DESCRIPTION RYM RKM 126-＊M/S101</td></tr><tr><td colspan="2">SEE SPECIFICATIONS</td><td colspan="2">APVD</td><td colspan="2">SCALE 1=1.5</td></tr></table>					MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT		RDS		DATE 06/08/09		DESCRIPTION RYM RKM 126-＊M/S101		SEE SPECIFICATIONS		APVD		SCALE 1=1.5		<table><tr><td colspan="2">FINISH</td><td colspan="2" rowspan="2">CONTACT TURCK FOR MORE INFORMATION</td><td colspan="4">UNIT OF MEASUREMENT</td><td colspan="2" rowspan="2">IDENTIFICATION NO.</td><td colspan="2" rowspan="2">REV </td></tr><tr><td colspan="2">SEE SPECIFICATIONS</td><td colspan="4">MILLIMETER [INCH]</td></tr></table>						FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT				IDENTIFICATION NO.		REV 		SEE SPECIFICATIONS		MILLIMETER [INCH]			
					MATERIAL				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT		RDS				DATE 06/08/09		DESCRIPTION RYM RKM 126-＊M/S101																											
SEE SPECIFICATIONS		APVD		SCALE 1=1.5																																										
FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT				IDENTIFICATION NO.		REV 																																				
SEE SPECIFICATIONS				MILLIMETER [INCH]																																										
<table><tr><td>I</td><td>UPDATE PROTECTION CLASS</td><td>CBM</td><td>04/13/21</td><td>76628</td></tr><tr><td>REV</td><td>DESCRIPTION</td><td>BY</td><td>DATE</td><td>ECO NO.</td></tr></table>					I	UPDATE PROTECTION CLASS	CBM	04/13/21	76628	REV	DESCRIPTION	BY	DATE	ECO NO.	<table><tr><td colspan="8">DO NOT SCALE THIS DRAWING</td><td colspan="2">FILE: 777024740</td><td colspan="2">SHEET 1 OF 1</td></tr></table>						DO NOT SCALE THIS DRAWING								FILE: 777024740		SHEET 1 OF 1															
I	UPDATE PROTECTION CLASS	CBM	04/13/21	76628																																										
REV	DESCRIPTION	BY	DATE	ECO NO.																																										
DO NOT SCALE THIS DRAWING								FILE: 777024740		SHEET 1 OF 1																																				