







VALVE END VIEW	MALE END VIEW	WIRING DIAGRAM	SPECIFICATIONS																								
 <p>1 = BLACK#1 2 = BLACK#2 3 = GREEN/YELLOW</p>	 <p>1 = N/C 2 = N/C 3 = BLACK#2 4 = BLACK#1 5 = GREEN/YELLOW</p> 	<p>VALVE</p> <p>P1</p> 	<table><tr><td>CONTACT CARRIER MATERIAL</td><td>NYLON OR TPU</td></tr><tr><td>MOLDED HEAD MATERIAL/COLOR</td><td>TPU/TRANSLUCENT BLACK (VALVE), YELLOW (P1)</td></tr><tr><td>CONTACT MATERIAL/PLATING (VALVE)</td><td>BRASS/SILVER</td></tr><tr><td>CONTACT MATERIAL/PLATING (P1)</td><td>BRASS/GOLD</td></tr><tr><td>COUPLING NUT MATERIAL/PLATING (P1)</td><td>BRASS/NICKEL</td></tr><tr><td>RATED CURRENT [A]</td><td>4.0 A</td></tr><tr><td>RATED VOLTAGE [V]</td><td>24 VDC</td></tr><tr><td>OUTER JACKET MATERIAL/COLOR</td><td>TPU/GRAY</td></tr><tr><td>CONDUCTOR INSULATION MATERIAL</td><td>PVC</td></tr><tr><td>NUMER OF CONDUCTORS [AWG]</td><td>3x18 AWG</td></tr><tr><td>OPERATING TEMPERATURE</td><td>-40°C to +90°C (-40°F to +194°F)</td></tr><tr><td>PROTECTION CLASS</td><td>MEETS NEMA 1,3,4,6P AND IEC IP67</td></tr></table>	CONTACT CARRIER MATERIAL	NYLON OR TPU	MOLDED HEAD MATERIAL/COLOR	TPU/TRANSLUCENT BLACK (VALVE), YELLOW (P1)	CONTACT MATERIAL/PLATING (VALVE)	BRASS/SILVER	CONTACT MATERIAL/PLATING (P1)	BRASS/GOLD	COUPLING NUT MATERIAL/PLATING (P1)	BRASS/NICKEL	RATED CURRENT [A]	4.0 A	RATED VOLTAGE [V]	24 VDC	OUTER JACKET MATERIAL/COLOR	TPU/GRAY	CONDUCTOR INSULATION MATERIAL	PVC	NUMER OF CONDUCTORS [AWG]	3x18 AWG	OPERATING TEMPERATURE	-40°C to +90°C (-40°F to +194°F)	PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67
CONTACT CARRIER MATERIAL	NYLON OR TPU																										
MOLDED HEAD MATERIAL/COLOR	TPU/TRANSLUCENT BLACK (VALVE), YELLOW (P1)																										
CONTACT MATERIAL/PLATING (VALVE)	BRASS/SILVER																										
CONTACT MATERIAL/PLATING (P1)	BRASS/GOLD																										
COUPLING NUT MATERIAL/PLATING (P1)	BRASS/NICKEL																										
RATED CURRENT [A]	4.0 A																										
RATED VOLTAGE [V]	24 VDC																										
OUTER JACKET MATERIAL/COLOR	TPU/GRAY																										
CONDUCTOR INSULATION MATERIAL	PVC																										
NUMER OF CONDUCTORS [AWG]	3x18 AWG																										
OPERATING TEMPERATURE	-40°C to +90°C (-40°F to +194°F)																										
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67																										





CABLE LENGTH	TOLERANCE *
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE *
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
* UNLESS OTHERWISE SPECIFIED	

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

D	UPDATE CABLE DIAMETER AND CABLE SPECS	RDS	05/06/14	44985
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
	MATERIAL SEE SPECIFICATIONS	DRFT RDS	DATE 04/26/13	DESCRIPTION VC8S 2-P669-*M	
FINISH SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	APVD A.A.	SCALE 1=1.3	IDENTIFICATION NO.	
		UNIT OF MEASUREMENT MILLIMETER [INCH]		REV D	
		DO NOT SCALE THIS DRAWING		FILE: 777031580	
				SHEET 1 OF 1	